

## New 816 Linear Actuator Limit Adjust Caps


**PRODUCT:** Nice 816 Linear Actuator

**DATE:** 11/22/2022

**SUBJECT:** Caps covering limit adjust screws have been changed.

### DESCRIPTION:

Two limit adjust screws on the rear of the 816 actuator motor housing are covered with protective caps (FIG-1). A better alternative cap (new P/N MX5571) has been sourced to replace the old screw-in cap and gasket (P/N MX71050005 and P/N 76010003).



**New Limit Adjust Cap  
(P/N MX5571)**

**FIG-1: Nice 816 Actuator Limit Switch Adjust  
Cap Location**

### REASON FOR CHANGE:


- Easier to install
- More durable
- Fewer components to handle

### CUSTOMER IMPACT:

- Longer lasting plug
- No concern of losing gasket
- No chance of stripping thread

### NOTICE

This bulletin is informational only, and no changes or actions are currently required in the field.



**FIG-2: Old Limit Adjust  
Cap & Gasket**

Contact Information: Call (253) 201-2918 for technical support. Visit <https://support.hysecurity.com/hc/en-us> for installation manuals, replacement part instructions, part diagrams and more. Qualified Nice | HySecurity distributors are experienced and trained to assist in resolving installation problems. For the name of a qualified distributor near you, call Nice | HySecurity at 800-321-9947. \*Before contacting your distributor or Nice | HySecurity Technical Support, obtain the serial number of your operator.